

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 12U, Black, 658H x 600W x 1070D mm

AR3103

Overview

Presentation An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 12U

Provided equipment Casters
Door
Key(s)
Leveling feet
Roof
Side Panels

Physical

Height 25.91 in (65.8 cm)

Width 23.62 in (60 cm)

Depth 42.13 in (107 cm)

Net Weight 130.01 lb(US) (58.97 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 36.25 in (92.08 cm)

Minimum Mounting Depth 7.52 in (19.1 cm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 600 lb(US) (272.16 kg) dynamic
600 lb(US) (272.16 kg) static

Conformance

Standards UL 2416
UL 60950-1

Ordering and shipping details

GTIN	731304347675
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31.30 in (79.5 cm)
Package 1 Width	45.67 in (116 cm)
Package 1 Length	29.53 in (75 cm)
Package 1 Weight	178.57 lb(US) (81 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)