

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 18U, Shock Packaging, Black, 925H x 600W x 1070D mm

AR3106SP

### Overview

<b>Presentation</b>	An industry-standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices. Shock pallet and shock packaging simplify IT "rack and stack" for equipment integrators.
<b>Lead time</b>	Usually in Stock

### Main

<b>Product or Component Type</b>	Rack enclosure
<b>Number of rack unit</b>	18U
<b>Provided equipment</b>	Casters Doors Key(s) Leveling feet Pallet ramps Reusable packaging Roof Side Panels

### Physical

<b>Height</b>	36.42 in (92.5 cm)
<b>Width</b>	23.62 in (60 cm)
<b>Depth</b>	42.13 in (107 cm)
<b>Net Weight</b>	159.00 lb(US) (72.12 kg)
<b>Color</b>	Black
<b>Mounting preference</b>	No preference
<b>Mounting Mode</b>	Not rack-mountable
<b>Maximum Mounting Depth</b>	36.25 in (92.08 cm)
<b>Minimum Mounting Depth</b>	7.52 in (19.1 cm)
<b>Rack Width</b>	19"
<b>Marking</b>	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
<b>Permanent permissible load</b>	900 lb(US) (408.23 kg) dynamic 900 lb(US) (408.23 kg) static

## Conformance

---

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Ordering and shipping details

---

GTIN	731304347705
------	--------------

## Packing Units

---

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	48.03 in (122 cm)
Package 1 Width	48.82 in (124 cm)
Package 1 Length	29.53 in (75 cm)
Package 1 Weight	279.99 lb(US) (127 kg)

## Offer Sustainability

---

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

---

Warranty	5 year repair or replace
----------	--------------------------

## Recommended replacement(s)