

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 42U, Shock Packaging, 2000 lbs, Black, 2124H x 750W x 1070D mm

AR3150SP

### Overview

**Presentation** NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

**Lead time** Usually in Stock

### Main

**Product or Component Type** Rack enclosure

**Number of rack unit** 42U

**Provided equipment** Baying hardware  
Documentation CD  
Key(s)  
Keyed-alike doors and side panels  
Leveling feet  
Mounting Hardware  
Pre-installed casters  
Side Panels

### Physical

**Height** 78.39 in (199.1 cm)

**Width** 29.53 in (75 cm)

**Depth** 42.13 in (107 cm)

**Net Weight** 343.83 lb(US) (155.96 kg)

**Color** Black

**Mounting preference** No preference

**Mounting Mode** Not rack-mountable

**Maximum Mounting Depth** 36.02 in (91.49 cm)

**Minimum Mounting Depth** 10.31 in (26.19 cm)

**Rack Width** 19"

**Marking** 14 gauge EIA mounting rail  
16 gauge front door  
16 gauge post  
16 gauge rear door  
18 gauge roof  
18 gauge side panels

**Permanent permissible load** 2250 lb(US) (1020.58 kg) dynamic  
3750 lb(US) (1700.97 kg) static

## Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

## Ordering and shipping details

GTIN	731304309888
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	85.79 in (217.9 cm)
Package 1 Width	52.01 in (132.1 cm)
Package 1 Length	43.50 in (110.5 cm)
Package 1 Weight	598.00 lb(US) (271.25 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

## Recommended replacement(s)