

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, Shock Packaging, 2000 lbs, Black, 2258H x 750W x 1070D mm

AR3157SP

Overview

Presentation NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

Lead time Usually Ships within 6 Weeks

Main

Product or Component Type Rack enclosure

Number of rack unit 48U

Provided equipment Baying hardware
Documentation CD
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting Hardware
Pre-installed casters
Side Panels

Physical

Height 88.90 in (225.8 cm)

Width 29.53 in (75 cm)

Depth 42.13 in (107 cm)

Net Weight 372.78 lb(US) (169.09 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 36.02 in (91.49 cm)

Minimum Mounting Depth 10.31 in (26.19 cm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
16 gauge post
16 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 2250 lb(US) (1020.58 kg) dynamic
3750 lb(US) (1700.97 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304309901
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	96.50 in (245.1 cm)
Package 1 Width	52.01 in (132.1 cm)
Package 1 Length	43.50 in (110.5 cm)
Package 1 Weight	625.01 lb(US) (283.5 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)