

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1200D mm

AR3307

Overview

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 48U

Provided equipment
Baying hardware
Key(s)
Leveling feet
Mounting Hardware
Pre-installed casters
Side Panels

Physical

Height 88.90 in (225.8 cm)

Width 23.62 in (60 cm)

Depth 47.24 in (120 cm)

Net Weight 329.70 lb(US) (149.55 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 41.73 in (105.99 cm)

Minimum Mounting Depth 7.50 in (19.05 cm)

Rack Width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
2250 lb(US) (1020.58 kg) dynamic
3750 lb(US) (1700.97 kg) static

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Ordering and shipping details

GTIN 731304256281

Country of origin CH

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 93.90 in (238.5 cm)

Package 1 Width 29.61 in (75.2 cm)

Package 1 Length 52.52 in (133.4 cm)

Package 1 Weight 364.76 lb(US) (165.45 kg)

Offer Sustainability

Sustainable offer status Green Premium product

REACH Regulation [REACH Declaration](#)

REACH free of SVHC Yes

EU RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Toxic heavy metal free Yes

Mercury free Yes

RoHS exemption information [Yes](#)

Take-back Take-back program available

Contractual warranty

Warranty 5 year repair or replace

Recommended replacement(s)