

Product data sheet

Specifications



APC NetShelter SX, Networking Rack Enclosure, 48U, Black, 2258H x 750W x 1200D mm

AR3347

Overview

Presentation NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 48U

Provided equipment Baying hardware
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting Hardware
Pre-installed casters
Side Panels
Vertical cable managers

Physical

Height 88.90 in (225.8 cm)

Width 29.53 in (75 cm)

Depth 47.24 in (120 cm)

Net Weight 408.85 lb(US) (185.45 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 37.75 in (95.89 cm)

Minimum Mounting Depth 11.00 in (27.94 cm)

Rack Width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
16 gauge post
16 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 2250 lb(US) (1020.58 kg) dynamic
3750 lb(US) (1700.97 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304284970
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	93.90 in (238.5 cm)
Package 1 Width	33.50 in (85.1 cm)
Package 1 Length	52.01 in (132.1 cm)
Package 1 Weight	458.96 lb(US) (208.18 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)