

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, Shock Packaging, 2000 lbs, Black, 2258H x 750W x 1200D mm

AR3357SP

Overview

Presentation NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

Lead time Usually Ships within 6 Weeks

Main

Product or Component Type Rack enclosure

Number of rack unit 48U

Physical

Height 88.90 in (225.8 cm)

Width 29.53 in (75 cm)

Depth 47.24 in (120 cm)

Net Weight 408.85 lb(US) (185.45 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 41.26 in (104.8 cm)

Minimum Mounting Depth 10.31 in (26.19 cm)

Rack Width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
16 gauge post
16 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
2250 lb(US) (1020.58 kg) dynamic
3750 lb(US) (1700.97 kg) static

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Ordering and shipping details

GTIN 731304309963

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 96.50 in (245.1 cm) |
| Package 1 Width | 52.01 in (132.1 cm) |
| Package 1 Length | 43.50 in (110.5 cm) |
| Package 1 Weight | 665.00 lb(US) (301.64 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Take-back | Take-back program available |

Contractual warranty

Warranty 5 year repair or replace

Recommended replacement(s)