

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, Black, 2258H x 750W x 1200D mm

AR3357

Overview

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 48U

Provided equipment
Baying hardware
Key(s)
Leveling feet
Mounting Hardware
Pre-installed casters
Side Panels

Physical

Height 88.90 in (225.8 cm)

Width 29.53 in (75 cm)

Depth 47.24 in (120 cm)

Net Weight 408.85 lb(US) (185.45 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 41.26 in (104.8 cm)

Minimum Mounting Depth 10.31 in (26.19 cm)

Rack Width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
16 gauge post
16 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
2250 lb(US) (1020.58 kg) dynamic
3750 lb(US) (1700.97 kg) static

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Ordering and shipping details

GTIN 731304259367

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	94.49 in (240 cm)
Package 1 Width	33.50 in (85.1 cm)
Package 1 Length	52.52 in (133.4 cm)
Package 1 Weight	444.94 lb(US) (201.82 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty 5 year repair or replace

Recommended replacement(s)