

Product data sheet

Specifications



APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, without Sides, Roofs, Doors, Black, 1991H x 600W x 806D mm

AR3812

Overview

Presentation Feature-rich enclosure specifically for the professional A/V market and optimized for cable management, power distribution, and airflow management.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

Number of rack unit 42U

Provided equipment Baying hardware
Documentation CD
Installation guide
Leveling feet
Mounting Hardware
Pre-installed casters

Physical

Height 78.39 in (199.1 cm)

Width 23.62 in (60 cm)

Depth 31.73 in (80.6 cm)

Net Weight 151.33 lb(US) (68.64 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 26.73 in (67.89 cm)

Rack Width 19"

Permanent permissible load 2250 lb(US) (1020.58 kg) dynamic
3000 lb(US) (1360.78 kg) static

Conformance

Standards UL 2416
UL 60950-1
EIA-310E

Ordering and shipping details

GTIN 731304284123

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.50 in (212.1 cm)
Package 1 Width	40.51 in (102.9 cm)
Package 1 Length	29.49 in (74.9 cm)
Package 1 Weight	182.39 lb(US) (82.73 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)