

# Product datasheet

Specifications



## Netshelter RX 42U Enclosure 800mm x 1200mm Medium Density without fan

AR5340

### Overview

**Presentation** A sealed IT enclosure to build up a Micro Data Center solution for industrial use and commercial applications which require dust and water protection. Designed for the integration of IT equipment and physical infrastructure components.

**Lead time** Usually in Stock

### Physical

**Height** 2006 mm

**Width** 800 mm

**Depth** 1212 mm

**Number of rack unit** 42U

**Minimum mounting depth** 22 mm

**Maximum mounting depth** 914 mm

**Baying included** No

**Permanent permissible load** 1361 kg static  
1022 kg dynamic

### Conformance

**IP degree of protection** IP54

**NEMA degree of protection** NEMA 12

### Packing Units

**Unit Type of Package 1** PCE

**Number of Units in Package 1** 1

**Package 1 Height** 213 cm

**Package 1 Width** 95 cm

**Package 1 Length** 132 cm

**Package 1 Weight** 286 kg

### Offer Sustainability

**Sustainable offer status** Green Premium product

**REACH Regulation** [REACH Declaration](#)

**REACH free of SVHC** Yes

---

<b>EU RoHS Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a>
<b>RoHS exemption information</b>	Yes

---

## **Contractual warranty**

---

**Warranty** 1 year

**Recommended replacement(s)**