

# Product data sheet

Specifications



## Horizontal Cable Organizer 1U w/ brush strip

AR8429



### Overview

|                     |  |
|---------------------|--|
| <b>Presentation</b> | This Horizontal Cable Organizer Promotes proper airflow while allowing cables to be passed from the front to the rear of the rack. Features plastic fingers at 1U increments for organized cable entry and exit. |
| <b>Lead time</b>    | Usually in Stock   |

### Main

|                            |                   |
|----------------------------|-------------------|
| <b>Number of rack unit</b> | 1U                |
| <b>Number of cables</b>    | 1                 |
| <b>Provided equipment</b>  | Mounting Hardware |

### Physical

|                            |                       |
|----------------------------|-----------------------|
| <b>Color</b>               | Black                 |
| <b>Height</b>              | 1.73 in (4.4 cm)      |
| <b>Width</b>               | 19.02 in (48.3 cm)    |
| <b>Depth</b>               | 0.59 in (1.5 cm)      |
| <b>Net Weight</b>          | 0.51 lb(US) (0.23 kg) |
| <b>Mounting Location</b>   | Front<br>Rear         |
| <b>Mounting preference</b> | No preference         |
| <b>Mounting Mode</b>       | Rack-mounted          |

### Ordering and shipping details

|             |              |
|-------------|--------------|
| <b>GTIN</b> | 731304208174 |
|-------------|--------------|

### Packing Units

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Unit Type of Package 1</b>       | PCE                    |
| <b>Number of Units in Package 1</b> | 1                      |
| <b>Package 1 Height</b>             | 3.90 in (9.9 cm)       |
| <b>Package 1 Width</b>              | 23.39 in (59.4 cm)     |
| <b>Package 1 Length</b>             | 1.50 in (3.8 cm)       |
| <b>Package 1 Weight</b>             | 0.84 lb(US) (0.379 kg) |

## Offer Sustainability

---

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| Take-back                  | Take-back program available   |

## Contractual warranty

---

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

## Recommended replacement(s)