



NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL: CLD CELL SPONGE

2. COLORS: BLACK

3. RoHS COMPLIANT

4. THIS PART IS UESD ON ARC12-70PX(R) RECEPTACLE WHERE X=A,B,C,D KEYS

5. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]

TITLE:

GASKET, RECEPTACLE, 70PIN, ARC SERIES

6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

	ARC7	70-GKT	-GKT		REF DRC70-GKT						
PART NUMBER			3	DESCRIPTION						ITEM	
QUANTITY			MAT	ERI	ALS LI	ST				_	
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 Fractions ±1/64		SIGNATURES		DATE	Amphonol						
		DRAWN:	LOUIE.YIN	01/AUG/22	Amphenol						
2 PL DEC ±0.30 3 PL DEC ±0.08	PL DEC ±0.15 Angles ±1°		ORION.LI	02/AUG/22 Sine Systems - www.amphenol-sine		nol-sine.co	m				
3) Note reference = X MATERIAL SPECIFICATIONS: PROCESS SPECIFICATIONS:		ENGINEER:			44724 Morley Drive						
		APPROVAL:	TOMMY.XIE	03/AUG/22	Clinton Township, MI 48036						
		CUSTOMER:				GASKET.RECEPTACLE.70PIN.ARC SERIES					
		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA			,			,			
		SPECIFICATIONS AND PERFORMAN SHOWN HEREON ARE THE PROPER THE AMPHENOL CORPORATION. NO OF REPRODUCTION ARE IMPLIED. A DIMENSIONS ARE SUBJECT TO NOF MANUFACTURING VARIATIONS.		ROPERTY OF ON. NO RIGHTS LIED. ALL	A C-	DWG NO:	ARC70-0	GKT		A1	
NEXT ASS'Y:				IS.	SCALE: NONE			SHEET 1	OF	1	