



AS SC-235 TL26



AS SC-235 TL26

E1441330

Assortment box Splicing connectors 250pcs 0.2-2.5mm²(4mm² Solid), AWG 28-12, with lever

Product Properties:

Nominal current	32 A
Nominal voltage	450 V
Number of clamp positions	2-5 .
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Suitable for solid core	Yes
Transparent	Yes
With operation lever	Yes
Colour	Green

Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-2.5 mm ²
Conductor cross section solid (solid, stranded)	0.2-4 mm ²
MOQ	1 .
Unit	pcs
Nominal cross section	0.2-4 mm ²
AWG-range	28-12 .
Nominal voltage	450 V

Approvals:

Compliance:**Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Terminal Blocks
Search Description	SKV2024ERIK3 ENR2023H
Alternative SKU	ASSC-235TL26

Logistic information:

Barcode	733117641338
Country of origin	CN
E-no	E1441330
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-235 TL26
Taric code	85369010
Unit	pcs