



## AVM FRITZ!Box 5530 wireless router Gigabit Ethernet Dual-band (2.4 GHz / 5 GHz) 4G White



Brand : AVM

Product code: 20002960

Product name : FRITZ!Box 5530

Wi-Fi 6 up to 2400 Mbit/s + 600 Mbit/s, Fiber optics up to 1000 Mbit/s (AON/GPON), Network with 1 x 2.5 gigabit LAN and 2 x gigabit LAN, For 6 cordless telephones, incl. answering machine, Easy to use and smart apps, Telephone system for IP-based connections

AVM FRITZ!Box 5530. Wi-Fi band: Dual-band (2.4 GHz / 5 GHz), Top Wi-Fi standard: Wi-Fi 6 (802.11ax), WLAN data transfer rate (max): 2400 Mbit/s. Ethernet LAN interface type: Gigabit Ethernet, Ethernet LAN data rates: 1000,2500 Mbit/s, Networking standards: IEEE 802.3bz. Mobile network generation: 4G. Security algorithms: WPS. Product type: Tabletop router, Product colour: White

Wireless LAN features		Ports & interfaces	
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	RJ-11 ports quantity	1
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	<b>Security</b>	
WLAN data transfer rate (max) *	2400 Mbit/s	Security algorithms	WPS
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)	Guest access	✓
<b>Network</b>		<b>Protocols</b>	
Ethernet LAN *	✓	DHCP server	✓
Ethernet LAN interface type *	Gigabit Ethernet	Universal Plug and Play (UPnP)	✓
Ethernet LAN data rates	1000,2500 Mbit/s	<b>Design</b>	
Networking standards	IEEE 802.3bz	Product colour	White
Dynamic DNS (DDNS)	✓	Product type *	Tabletop router
<b>Mobile network</b>		<b>Packaging content</b>	
Mobile network generation	4G	Cables included	Fiber, LAN (RJ-45)
3G	✗	<b>Antenna</b>	
4G	✗	Antenna design *	Internal
<b>Ports &amp; interfaces</b>		<b>Weight &amp; dimensions</b>	
Ethernet LAN (RJ-45) ports *	3	Width	208 mm
USB port *	✗	Depth	150 mm
		Height	37 mm