

# 10.4" LED Monitor with BNC Input

Art. no. TVAC10001

Page 1 of 1



- Resolution: 800 x 600 pixels
- Connections: 1 x HDMI, 1 x VGA, 1 x BNC input, 1 x BNC output, 1 x audio input
- High contrast 10.4" LED monitor (4:3 format)
- Integrated loudspeaker
- Compatible with VESA brackets
- Compact dimensions: ideal for checkout areas, for example

## Technical Data:

Dimensions	(W x H x D) 268 x 222 x 29 mm
Connection type	1 x HDMI, 1 x VGA, 1 x BNC in, 1 x BNC out, 1 x Audio
Picture format	4:3
Screen diagonal	10,4 "
Width	268 mm
Display surface	Matte
Color levels	16,7 MIO
Frequency range	31,5 – 80KHz (H) / 56 – 75Hz (V) GHz
Housing material	Plastic
Brightness	300 cd/m <sup>2</sup>
Height	222 mm
Comb filter	3D
Length	29 mm
Loudspeaker	Integrated, 2x2.5 W, stereo

Power consumption	11,5 W
Max. operating temperature	40 °C
Max. humidity	70 %
Min. operating temperature	-10 °C
Monitor type	Standard TFT LCD
Net weight	1,2 kg
Pixel pitch	0,264 x 0,265 (H) x (V) mm
Reaction time	8 ms
Signal detection	Automatic
DC voltage supply	12 V
Power consumption	1.500 mA
Video system	PAL / NTSC