

Smartvest Wireless Siren

Art. no. FUSG35000A

Page 1 of 2



- Smartvest extension for sounding alarms indoors and outdoors
- Quick and cable-free installation without the need for wires thanks to battery operation
- High-volume siren (up to 100 dB) and red LED strobe light for alarms with deterrent effect
- Sturdy, weatherproof siren (IP44)
- Automatic supervision, with functional tests repeated daily and feedback sent to the Smartvest alarm control panel
- Low battery notification sent to the Smartvest alarm control panel
- Battery life of up to 2 years
- Tamper protection provided by anti-removal wall contact

To be able to provide alarming both indoors and outdoors, the Smartvest Wireless Siren is fitted with a loud siren (up to 100dB) and a red LED strobe light. Battery operation (battery life: up to two years) means no wiring is required during installation; when the battery is low, the alarm panel is notified immediately. To be able to guarantee real security, the Smartvest Wireless Siren is fitted with tamper protection in the form of an anti-removal wall contact.

Smartvest Wireless Siren

Art. no. FUSG35000A

Page 2 of 2

Technical Data:

Areas of usage	Outside / Inside
Color	White
Compatible with Secvest	No
Compatible with Smartvest	Yes
Power consumption Standby	0,2 mA
Min. humidity	10
Dimensions	(B x L x H) 112 x 122 x 300 mm
Alarming	Acoustic warning signal
Battery operation	Yes
Battery type	C (1,5V)
Gross weight	0,19 kg
Wireless modulation	FSK
Radio frequency	868 MHz
Wireless range	(Depending on installation) 30 - 100 m
Housing material	Plastic
Battery quantity	4
Luminous color	Red

Illuminant	LED
Max. battery life	1 y
Max. operating temperature	50 °C
Max. humidity	80 %
Min. operating temperature	-10 °C
Net weight	0,82 kg
Tamper protection	Yes
Sound pressure	100 dB
IP protection class	44
Transmission power	4,5 dBm
DC voltage supply	5 V
Connector type	DC-plug: 3,5 x 1,35mm
Power consumption	200 mA