

Smartvest Wireless Door Bell

Art. no. FUSG35010A

Page 1 of 2



- Smartvest extension for signalling indoors
- Five door bell/signal tones (four door bell tones, one alarm tone), which can be configured individually (i.e. assignment of sensor to door bell tone)
- Volume can be set at three different levels
- Can also be used for signalling in the event of an alarm
- Automatic supervision with functional tests repeated daily and feedback sent to the Smartvest alarm control panel
- Visual feedback via blue LED when starting up and in use
- Low battery notification sent to the Smartvest alarm control panel

The Smartvest Wireless Door Bell is a Smartvest extension for signalling indoors. The door bell supports five different signal tones and can play the signals at three different volumes (four door bell tones, one alarm tone). The triggers for a signal can be individually configured. This means that the Wireless Door Bell is suitable for use as a door bell and a sounder. Automatic supervision (functional tests repeated daily) to the alarm control panel means that you can monitor the door bell's functionality at all times and can react to a low battery in good time.

Smartvest Wireless Door Bell

Art. no. FUSG35010A

Page 2 of 2

Technical Data:

Areas of usage	Inside
Color	White
Compatible with Secvest	No
Compatible with Smartvest	Yes
Power consumption Standby	0,0265 mA
Min. humidity	10
Dimensions	(B x L x H) 60 x 28 x 105 mm
Alarming	Acoustic warning signal
Display	LED
Battery operation	Yes
Battery type	AA (1,5V)
Gross weight	0,19 kg
Adjustable alarm tone	5 Gong tones
Wireless modulation	FSK
Radio frequency	868 MHz

Wireless range	(Depending on installation) 30 - 100 m
Housing material	Plastic
Battery quantity	3
Max. battery life	1 y
Max. operating temperature	40 °C
Max. humidity	80 %
Min. operating temperature	-10 °C
Net weight	0,145 kg
Tamper protection	No
Sound pressure	60 / 70 / 80 dB
Transmission power	4,5 dBm
Power consumption	265 mA