

363MM7

Industrial Switched Interlocked Socket Outlet

2CMA168037R1000

Switched Interlocked Socket Outlet, metal, earthing sleeve position 7h, rated current 63A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Switched Interlocked Socket Outlet
Product ID	2CMA168037R1000
Function	Switched Interlocked Socket Outlet, metal
EAN	739269663
Catalog Description	Switched interlocked socket-outlet, 7h, 63A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421373
E-Number Norway	2417108
E-Number Sweden	E2417108
Standards	IEC 60309-1, -2, -4
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	165 millimetre
Product Net Height	177 millimetre
Product Net Length	228 millimetre
Product Net Depth	228 millimetre
Product Net Weight	2.5 kilogram

TECHNICAL

Product Main Type	CMM
Color	Black
Number of Poles	4
Clock Position	7Hour
Rated Current	63 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm ²
Housing Material	Aluminium
Plug Angle	
Product Group	Critical&Safe

PACKAGING

Package Width	170 millimetre
Package Height	185 millimetre
Package Gross Weight	2.67 kilogram
Package Length	300 millimetre
Package Units	box 1 piece