

332MVS3W

# Industrial Switched Interlocked Socket Outlet

## 2CMA167876R1000

Switched Interlocked Socket Outlet, vertical, earthing sleeve position 3h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code red



## GENERAL

<b>Product Name</b>	Industrial Switched Interlocked Socket Outlet
<b>Product ID</b>	2CMA167876R1000
<b>Function</b>	Switched interlocked socket outlet, vertical
<b>EAN</b>	7392696678766
<b>Catalog Description</b>	Switched interlocked socket-outlet, 3h, 32A, IP67, 3P+E
<b>Country of Origin</b>	Czech Republic (CZ)
<b>E-Number Finland</b>	2416978
<b>E-Number Norway</b>	2416978
<b>E-Number Sweden</b>	2416978
<b>Standards</b>	IEC 60309-1, -2, -4
<b>RoHS Status</b>	Following EU Directive 2011/65/EU

## DIMENSIONS

<b>Product Net Width</b>	120 millimetre
<b>Product Net Height</b>	149 millimetre
<b>Product Net Length</b>	243 millimetre
<b>Product Net Depth</b>	243 millimetre
<b>Product Net Weight</b>	0.72 kilogram

## TECHNICAL

<b>Product Main Type</b>	CMVS
<b>Color</b>	Red
<b>Number of Poles</b>	4
<b>Clock Position</b>	3Hour
<b>Rated Current</b>	32 ampere
<b>Rated Voltage</b>	380/440 volt
<b>Frequency</b>	50/60 hertz
<b>Degree of Protection</b>	IP67
<b>Cable Cross-Section</b>	2.5...10 mm <sup>2</sup>
<b>Housing Material</b>	Thermoplastic (PBT)
<b>Plug Angle</b>	
<b>Product Group</b>	Critical&Safe

## PACKAGING

<b>Package Width</b>	152 millimetre
<b>Package Height</b>	265 millimetre
<b>Package Gross Weight</b>	0.8 kilogram
<b>Package Length</b>	120 millimetre
<b>Package Units</b>	box 1 piece