



Anybus ProfiTrace Toolkit Plus

Item number: 37021

ProfiTrace is an essential tool for maintenance and troubleshooting and is currently the most powerful mobile analyzer for PROFIBUS networks.



This tool enables network measurements to troubleshoot issues on running production.

Features and benefits

- ✓ **Portable tool that fits in your pocket**
The ProfiCore is a mobile hardware tool that is easy to carry and ready with 2 simple connections.
- ✓ **Gain insight into your full network**
Once connected to the network, you will be able to control and measure the entire installation.
- ✓ **Available when you need it**
Measurements can be performed at any time, no shutdown of the network is required. Simply measure PROFIBUS DP and PA segments.
- ✓ **Show your results to make the change**
All analysis can be compiled in a detailed report that contains the signals of all devices, faults, network topology, bar graph and administrative information.

Anybus ProfiTrace Toolkit Plus



General

Net Weight (g)	1394 g
Packed Width ERP (mm)	8 mm
Packed Height ERP (mm)	26 mm
Packed Depth ERP (mm)	33 mm
Packed Weight ERP (g)	1394 g
Operating Temperature °C Min	0
Operating Temperature °C Max	60
Storage Temperature °C Min	-20
Storage Temperature °C Max	70
Input Voltage (V)	5V
Power Connector	USB
Housing Materials	Plastic
Packaging Material	Cardboard
Warranty (years)	1 year

Identification & Status

Product ID	37021
Country of Origin	Netherlands (the)
HS Code	9031808000
Export Control Classification Number (ECCN)	EAR99
Supply Risk Factor ERP	Volume not defined yet

Anybus ProfiTrace Toolkit Plus



Identification & Status

Purchasing Multiple ERP	1
-------------------------	---

Certifications & Standards

Protection Class IP	IP20
---------------------	------

WEEE Category	IT and telecommunications equipment
---------------	-------------------------------------