

## **AXIS W700 Docking Station 1-bay**

AXIS W700 Docking Station 1-bay enables easy handling of the body worn camera with fast charging, quick, secure and easy data offloading.

- > Grab and go, ready when you are
- > Dock and go, for automatic reliable offloading and fast charging
- > Reliable docking connectors
- > Splash proof



T10142275/EN/M2.2/2010 www.axis.com

## AXIS W700 Docking Station 1-bay

Network	
Supported protocols	IPv4, IPv6 USGv6, HTTPS, Bonjour, DNS, NTP, TCP, UDP, ICMP, DHCP, ARP
Throughput	100 Mbit/s
General	
Capacity	1 bay
Casing	Plastic casing Color: black NCS S 9000-N
Sustainability	PVC free
Power	4.8-5.2 V DC, max 9 W
Connectors	Shielded RJ45 10BASE-T/100BASE-TX DC input Pogo pin pads
Operating conditions	0 °C to 40 °C (32 °F to 104 °F) Humidity 10–85% RH (non-condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F) Humidity 10-85% RH (non-condensing)

Approvals	EMC
	EN 55032 Class B, EN 55035, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-3(B)/NMB-3(B), RCM AS/NZS CISPR 32 Class B Safety
	IEC/EN/UL 62368-1
	Environment IEC 60068-2-1, IEC 60068-2-14, IEC 60068-2-2, IEC 60068-2-78 Network Compatible with NIST SP500-267 throughput
Dimensions	Height: 47 mm (1.9 in)
	Width: 76 mm (3.0 in)
	Depth: 95 mm (3.8 in)
Weight	130 g (0.29 lb)
Warranty	3-year warranty, see axis.com/warranty

Environmental responsibility: axis.com/environmental-responsibility

