

blanking plug B-M3-S9

Part number: 30979

★ Core product range

As per DIN 908, with sealing ring.

FESTO



Data sheet

Feature	Value
Container size	10
Nominal tightening torque	0.48 Nm
Tolerance for nominal tightening torque	± 55 %
Product weight	1 g
Mounting type	External hex A/F 4.5 Slot 0.8 mm
Pneumatic connection, port 1	Male thread M3
Materials note	Free of copper and PTFE Conforms to RoHS
Material blanking plug	High alloy steel, non-corrosive
Material o-ring	Stainless steel NBR