



B191

**BahcoFit Slotted Straight
Screwdrivers with Rubber Grip
2.5-6.5 mm**



PRODUCT DETAILS

- For slotted head screws, electrician's blade
- Black oxide tip for higher accuracy
- Two-component handle with vertical grooves and large soft-grip area for comfortable grip and high torque transfer
- Handle made with over 75% rubber
- Anti-slip surface
- Permanent symbol and markings on the handle for quick identification of the tip
- Integrated hanging hole
- Chrome plated blade for high protection against corrosion, long life tool
- High-performance alloy steel blade
- Standards: ISO 2380 and DIN 5264
- SB coding for retailed packed on a plastic hanger



Follow the Fish!



PRODUCT ATTRIBUTES

Product								
B191.025.075	0.4 mm	2.5 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm	20 g
B191.030.075	0.5 mm	3 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm	35 g
B191.030.100	0.5 mm	3 mm	100 mm	3 mm	24,5 mm	95 mm	195 mm	36 g
B191.030.200	0.5 mm	3 mm	200 mm	3 mm	24,5 mm	95 mm	295 mm	40 g
B191.035.100	0.6 mm	3.5 mm	100 mm	3.5 mm	24,5 mm	95 mm	195 mm	39 g
B191.040.100	0.8 mm	4 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm	44 g
B191.040.125	0.8 mm	4 mm	125 mm	4 mm	24,5 mm	95 mm	220 mm	47 g
B191.040.250	0.8 mm	4 mm	250 mm	4 mm	24,5 mm	95 mm	345 mm	60 g
B191.055.125	1 mm	5.5 mm	125 mm	5.5 mm	30 mm	105 mm	230 mm	70 g
B191.055.150	1 mm	5.5 mm	150 mm	5.5 mm	30 mm	105 mm	255 mm	79 g
B191.055.300	1 mm	5.5 mm	300 mm	5.5 mm	30 mm	105 mm	405 mm	105 g
B191.065.150	1.2 mm	6.5 mm	150 mm	6.5 mm	34 mm	117 mm	267 mm	110 g
B191.065.300	1.2 mm	6.5 mm	300 mm	6.5 mm	34 mm	117 mm	417 mm	140 g
SB191.025.075	0.4 mm	2.5 mm	75 mm	2.5 mm	24,5 mm	95 mm	170 mm	24 g
SB191.030.075	0.5 mm	3 mm	75 mm	3 mm	24,5 mm	95 mm	170 mm	39 g
SB191.030.100	0.5 mm	3 mm	100 mm	3 mm	24,5 mm	95 mm	195 mm	40 g
SB191.030.200	0.5 mm	3 mm	200 mm	3 mm	24,5 mm	95 mm	295 mm	45 g
SB191.035.100	0.6 mm	3.5 mm	100 mm	3.5 mm	24,5 mm	95 mm	195 mm	43 g
SB191.040.100	0.8 mm	4 mm	100 mm	4 mm	24,5 mm	95 mm	195 mm	48 g
SB191.040.125	0.8 mm	4 mm	125 mm	4 mm	24,5 mm	95 mm	220 mm	51 g
SB191.040.250	0.8 mm	4 mm	250 mm	4 mm	24,5 mm	95 mm	345 mm	64 g
SB191.055.125	1 mm	5.5 mm	125 mm	5.5 mm	30 mm	105 mm	230 mm	74 g
SB191.055.150	1 mm	5.5 mm	150 mm	5.5 mm	30 mm	105 mm	255 mm	83 g
SB191.055.300	1 mm	5.5 mm	300 mm	5.5 mm	30 mm	105 mm	405 mm	109 g
SB191.065.150	1.2 mm	6.5 mm	150 mm	6.5 mm	34 mm	117 mm	267 mm	114 g
SB191.065.300	1.2 mm	6.5 mm	300 mm	6.5 mm	34 mm	117 mm	417 mm	144 g

