


LSA+ Type IDC Contacts



LSA+ Type IDC Contacts, 5.08mm pitch, 3 Way and 4 Way (B238, B239) 3 way and 4 way PCB mount IDC contacts for LSA+ connections.

Features:

- Termination using LSA+ type punch down tool. No need for soldering or screw terminations
- Includes PCB mount retaining posts for heat staking, ensuring a secure fit
- Pitch of 5.08mm between contacts
- Voltage rating of 60V AC RMS
- Operating temperatures from -20° to 125°
- · Suitable for wave soldering
- Known by BT codes 238A and 239A

Specifications:

Net weight (including primary packaging):

B238: 1.65 g
 B238#20: 34.5g
 B239#20: 42.3g
 B238#50: 82.50
 B239#50: 141.50
 B238#100: 165.6g
 B239#100: 212.3g

Dimensions:

B238 (3 way): 16.72 x 21.8 x 7.2 mm
 B239 (4 way): 16.9 x 21.8 x 7.2 mm

Colour: white

Materials:

o Housing: PC UL94V-0

Contacts: Phosphor bronze with tin plating

Packaging: packaged in poly bags of 50, or cartons of 1000

Commodity code: 85366930

EAN: B238: 5055386510075 B239: 5055386510082 **Country of Origin:** China

B238#20: 5055386510334 B239#20: 5055386510358 B238#50: 5055386510105 B239#50: 5055386510341 B239#100: 5055386510365

.5386510341 B239#100: 5055386510365 14/11/2022




B238





B239





Code: B238, B239 **ROHS Compliant**

















NOTES:
1. HOUSING: PC UL94V-0
2. CONTACT: PHOSPHOR BRONZE WITH SILVER PLATING
3. WIRE: CABLE SIZE:
SOLID COPPER WIRES UP TO 0.4 mm - 0.8 mm IN DIA.

PE OR PVC INSULATED WIRE (100% PE/FOAM SKIN, FILLED/UNFILLED)
UP TO 1.4 mm IN DIAMETER

4. CONTACT RESISTANCE: 10 MILLIOHMS MAX.

5. VOLTAGE RATING: 250 VDC
6. OPERATING TEMPPERATURE: -20°C TO +125°C AND HUMLDITY UP TO 95%
7. INSULATION RESISTANCE: 500 VDC, VOLTAGE APPLIED 5000 MEGOHMS MIN.
8. DIELECTRIC STRENGTH: AC 2000 VRMS