

Specification - BRIO 500

Product Dimensions				
Component	Height	Length	Depth	Weight
Webcam	1.2 in (31.5 mm)	4.3 in (110 mm)	1.2 in (31.5 mm)	4.2 oz (121 g), incl. mount clip & cable
Webcam w/mount clip	2 in (51.5 mm)	4.3 in (110 mm)	1.8 in (45 mm)	
Mount clip	1 in (25 mm)	1.8 in (45.8 mm)	2.6 in (65.1 mm)	1.4 oz (40 g), incl. removable mount adapter
Cable		Attached cable length: 5 ft (1.5 m)		

Product Specifications	
System Requirements	<p>Required: Available USB-C port</p> <p>Works with: Windows, macOS, or Chrome OS*, and virtually any popular videocalling platform.</p> <p>*Logi Tune not available for Chrome OS *RightSight currently available only for Windows</p> <p>Certified for: Microsoft Teams, Zoom, Google Meet, Works With Chromebook.</p> <p>Compatible with:</p> <ul style="list-style-type: none">• Windows 8 or later (Windows 8.1 or later required for resolutions greater than 1080p)• macOS 10.10 or later• Chrome OS <p>(2GB RAM or more needed for 1080p video streaming and 1GB RAM is typically needed for streaming 720p)</p>

Product Specifications

Technical Specifications

Multiple resolutions

- 1080p/30fps (1920x1080 pixels)
- 720p/60fps (1280x720 pixels)
- Camera megapixel 4MP
- Focus type: Autofocus
- Lens type: Glass

Built-in Microphone type

- Stereo microphone
- Mic range: Upt to 4 ft (1.22 m)
- Diagonal field of view (dFoV): 90°/78°/65°

Rightlight 4 with HDR for clear image in various lighting environments ranging from low light to direct sunlight.

- Hardware zoom: 4x Digital zoom
- Integrated privacy shutter
- USB connectivity: USB-C plug-and-play
- The detachable universal mounting clip fits laptops, LCD displays, or monitors
- Supported in Logi Tune

Package Contents

- BRIO 500 with attached USB-C cable
- Mount clip with removable mount adapter
- User documentation