

Previously known as: Scorpio™ 08-354

## Neoprene safety gloves with a rough finish, for enhanced grip in wet, slippery conditions

- **Advanced protection:** AlphaTec® 08-354 chemical-resistant gloves are 100% impermeable to liquid, guarding against varying hazardous chemicals and liquids, averting a variety of potential workplace injuries
- **Heightened grip:** With a textured finish, these medium-duty work gloves enable wearers to securely handle wet or slippery parts with ease, thereby increasing worker productivity
- **Elevated comfort:** Owing to their soft and stretchable cotton liner, AlphaTec® 08-354 protective gloves cushion the hand and absorb moisture, reducing excessive chafing
- **Increased flexibility:** These neoprene gloves are also particularly flexible, dexterously facilitating object handling and enabling simpler donning and removal, for lesser hand fatigue



### Industries

- Automotive
- Chemical
- Logistics
- Machinery and Equipment
- Warehousing

### Applications

- Equipment repair & maintenance
- Warehousing of raw materials
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process

Previously known as: Scorpio™ 08-354

### Key Features

- **Neoprene coating:** Advanced liquid and chemical protection
- **Rough finish:** Enhanced grip performance, for greater efficiency
- **Interlock cotton knit liner:** For soft, dexterous work gloves

### Vulcanization Chemical Accelerators

- Zinc Dibutyldithiocarbamate (ZDBC)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards

ANSI/ISEA 105-2024



EN388: 2016



3121B

EN 407



XIXXXX

EN ISO 374-5:2016



### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                  | SIZE     | LENGTH   | COLOR | PACKAGE                                  |
|------------------|------------------------------------------------------------------------------|----------|----------|-------|------------------------------------------|
| AlphaTec® 08-354 | <b>Liner Material:</b> Interlock cotton<br><b>Coating Material:</b> Neoprene | 8, 9, 10 | 355 / 14 | Green | • 12 pairs in a box ,6 boxes in a carton |

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.