

Previously known as: MICROGARD 1800 STANDARD - Model 111

Lightweight, breathable protective suit, providing moderate chemical protection.

- **Specialized protection:** The AlphaTec® 1800 STANDARD Bound - Model 111's low-linting fabric offers wearers light chemical resistance*, reducing cross contamination risks and guarding against low-hazard liquid spray and fine particulates
- **Limited surface defect risks:** Being silicone-free, the risk of contaminant transfer to metal before painting is lessened
- **Added defenses:** Its bound seams enhance overall robustness and barrier protection
- **Assured antistatic capabilities:** It meets AATCC 76 and EN 1149-5 antistatic standards
- **Heightened breathability:** Microporous polyethylene laminate makes this protective body suit water vapor-permeable, for relief from heat stress
- **Enhanced fit and features:** This protective outer garment's optimized fit enhances comfort, while a three-piece hood extends coverage and a two-way front zipper and resealable storm flap boost practicality

*this protective suit delivers CE Category III Type 5/6 protection



Industries

- Life Sciences
- Automotive
- Metal fabrication
- Food Processing
- Chemical
- Automotive Aftermarket
- Mining


Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Fibre Glass Resin Applications
- Handling of powders


KEY FEATURES & BENEFITS

- **Low-linting fabric:** Resists fine particulates and low-hazard liquid spray
- **Silicone-free design:** Spray-painting application-friendly
- **Bound seams:** Superior strength and barrier protection

Material Diagram



Seam Diagram



Performance Standards


0598



EN ISO 13688:2013


TYPE 5


TYPE 6

Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL, 4XL, 5XL
Color	White
Country Of Origin	China, Sri Lanka
Fabric Thickness	100
Packaging Overview	Individually Packed
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	1800 STANDARD - Model 111
Standards Overview	CE CATEGORY III (Type 5, Type 6, EN 1149-5)
Seam Type	Bound
Shelf Life	5 years
Style Number	W18B111

Suit components & accessories

Suit Components and Accessories	
Design Features	Coverall, 3-piece hood, 2-way front zipper with re-sealable storm flap. Elasticated hood, waist, wrists and ankles.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

