

Previously known as: MICROGARD® 2000 STANDARD - Model 111

### Superior, breathable microporous laminate suit, perfected for industrial applications.

- **Specialized protection:** The AlphaTec® 2000 STANDARD Bound - Model 111 grants wearers moderate chemical protection\*, resisting liquid and particulate biological hazards (including radioactive particulates\*\*)
- **Added defenses:** This protective body suit also meets EN 14126 and ASTM F1670/1671 standards for bloodborne pathogen protection and DIN 32781 requirements for pesticide resistance
- **Advanced breathability:** The use of microporous polyethylene laminate nonwoven fabric makes it water vapor-permeable, reducing heat stress
- **Assured antistatic capabilities:** In addition, this protective suit satisfies EN 1149-5 antistatic standards
- **Reduced cross contamination risks:** Low-linting fabric lessens cross contamination risk in critical areas
- **Limited allergy and surface defect risks:** Latex- and silicone-free by design, risks of Type IV latex allergies or contaminant transfer to metal when spray-painting are minimized
- **Enhanced fit and features:** This chemical-protective suit's optimized fit and finger loops enhance comfort and user-friendliness, while a three-piece hood provides added protection and a two-way front zipper with resealable storm flap enhance practicality

\*CE Category III Type 5/6 protection

\*\*in accordance with EN 1073-2 standards




## Industries

- Life Sciences
- Automotive
- Metal fabrication
- Food Processing
- Defense
- Agriculture
- Automotive Aftermarket
- Chemical
- Emergency Medical Services
- Machinery and Equipment
- Oil and gas
- Utilities

## KEY FEATURES & BENEFITS

- **Protective barrier:** Enhanced personal protection
- **Microporous laminate fabric:** Reduced risk of heat stress
- **EN 14126 and ASTM F1670/1671-certified:** Resists bloodborne pathogen

## Material Diagram




## Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Cleaning of plant and machines

## Technology



## Seam Diagram



Performance Standards

  
0598



  
TYPE 5-B

  
TYPE 6-B

  
EN 1073-2



  
EN 14126

  
DIN 32781



EN ISO 13688:2013

Product Information

| Product Information |                                                    |
|---------------------|----------------------------------------------------|
| Available Sizes     | S, M, L, XL, 2XL, 3XL, 4XL, 5XL, XS, 6XL, 7XL, 8XL |
| Color               | White, Green                                       |
| Country Of Origin   | China, Sri Lanka                                   |
| Models Available    | 102, 103, 113, 122, 162                            |
| Packaging Overview  | Individually Packed                                |
| Product Material    | Microporous polyethylene Laminate non-woven        |
| Product Reference   | 2000 STANDARD - Model 111                          |
| Seam Type           | Bound                                              |
| Shelf Life          | 5 years                                            |
| Style Number        | W20B111, G20B111                                   |

Suit components & accessories

| Suit Components and Accessories |                                                                                                                        |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Design Features                 | 3-piece hood, 2-way front zipper with resealable storm flap, finger loops. Elasticated hood, waist, wrists and ankles. |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444

**Australia**  
Ansell Limited  
T: +61 1800 337 041

**Asia Pacific Region**  
Ansell Global Trading Center  
T: +603 8310 6688

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.