



BW 70.29

- For DIN-rail mounting
- Flush mount dimensions 45 x 35 mm
- Bx 70.29: without terminal cover
- Bx 70.89: with terminal cover
- Screw terminals (pull-up type)
- Touch proof connections
- With operation indicator (flashing LED)
- One Version for 50 and 60 Hz

## Elapsed time counters BW/BG 70.29/70.89

for DIN-rail or wall mounting · Alternating/Direct Current [paladin 311270-311280/312270-312280]





Technical data	<b>BW 70.x9</b> paladin <b>311 2x0</b> Alternating current	<b>BG 70.x9</b> paladin <b>312 2x0</b> Direct current	
<b>Supply voltages</b> (please state when ordering)	230 V, 50–60 Hz (standard) 115 V, 50–60 Hz 24 V, 50–60 Hz	12-48 VDC	
Special voltages	-	5–24 VDC, 36–120 VDC, 100–300 VDC	
Other voltages	on request	-	
Voltage tolerance	±15%	±10%	
Power consumption (real power)	0,26 W	approx. 20 mW at 12 VDC	
Counter capacity	99,999 h.	99,999 h.	
Accuracy of reading	0.1 h.	0.1 h.	
Numeral height	4.4 mm	4.4 mm	
Numeral colour	white, decimal figure red	white, decimal figure red	
<b>Operation indicator</b> (without reset)	flashing LED	flashing LED	
Permitted ambient temperature	–15°…+55°C	-10°+50°C	
Enclosure	self-extinguishing thermopl	self-extinguishing thermoplastic	
Type of connection	Screw terminals	Screw terminals	
Type of protection (DIN EN 60529)	IP 50 to DIN EN 60529	IP 50 to DIN EN 60529	
Class of protection	II (when fitted in accord- ance with regulations)	III (up to 48 VDC)	

## Accessories

Terminal cover for Bx 70.29 (wall mounting)

003.008.004

Order numb	er	Version	
BW 70.29	Paladin 311 270	Alternating current, without terminal cover	
BG 70.29	Paladin 312 270	Direct current, without terminal cover	
BW 70.89	Paladin 311 280	Alternating current, with terminal cover	
BG 70.89	Paladin 312 280	Direct current, with terminal cover	

Housing colour

121345