

CATV Amplifier 20 dB 86-862 MHz 2 Outputs

General information

Antenna amplifier with adjustable gain control for digital and analogue antenna signals.

Specifications

Power consumption in operating mode:	5 W
Gain control:	10-20 dB
Frequency range:	86-862 MHz
Return frequency range:	5-65 MHz
Impedance:	75 Ohm
Gain:	20 dB
Noise figure:	4 dB
No. of inputs:	1
Return path:	Passive
No. of outputs:	2
Colour:	White
Usage:	Indoor
Power plug:	Euro / Type C (CEE 7/16)
Application:	CATV
Input voltage:	AC 220 - 240 V, 50/60 Hz
Connector type:	F-connector

Package contents

Supplied F-Connector & IEC coax adapters provide a flexible installation. Adjustable 20dB gain amplifier per output. Suitable for wallmounting.



Sales information

Order code:	BYD1102EC
Product description:	CATV Amplifier 20 dB 86-862 MHz 2 Outputs
Packaging:	Blister
Brand name:	Bandridge



Quantity	LxWxH (mm)	Weight
1	120x65x235	353 gr.
10	250x250x355	3780 gr.
40	380x515x505	16100 gr.