

AR48 GY4 12V 20W 10D ALU 2000h 41900SP

Article number 145387

BEE AR48 GY4 12V 20W 10D Aluminium 2000h 48x38mm without anti-glare Low voltage halogen reflector lamp

Brilliant accent. This lamp can be used in shops, restaurants, hotels, offices and public buildings.



General ETIM properties

ETIM group	Lamps
ETIM class	Low voltage halogen reflector lamp
Name	145387
Brand	Bailey
Productseries	Halogen reflector LV
Product type	AR48

ETIM specifications

Lamp designation	AR48
Average nominal lifespan [h]	2000
Weighted energy consumption in 1000 hours [kWh]	20
Energy efficiency class	C
Neodym-lamp	No
Xenon	No
Cool beam	No
Colour	Colourless
Luminous intensity [cd]	3100
UV-protection	No
Low-pressure technique	No
Reflector type	Dichroid plated glass
Axial filament	No
Total length [mm]	38
Diameter [mm]	48
Front glass	No
Infrared coating/-technique	No
Colour temperature [K]	2800
Beam angle [°]	10
Socket	GY4
Lamp voltage [V]	12 - 12
Lamp power [W]	20

Alternative articles



145245