

LED U-FIL T22X57 Ba15d 1W (6W) 55lm 827 Clear

Article number 80100038297

BAI LED U-Filament Tube T22 Ba15d 1W 2700K Clear 55lm (6W) 230V-240V 360°
22x57mm LED-lamp

As a specialist, Bailey needs to maintain their reputation in the field of compact lamps. These durable compact LED lamps are often used in elegant fixtures where there is little space for the light source.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	80100038297
Brand	Bailey
Productseries	LED Filament tube
Product type	T22x57

ETIM specifications

IFTTT support available	No
Compatible with Amazon Alexa	No
Compatible with Google Assistant	No
Compatible with Apple HomeKit	No
Photobiological safety according to EN 62471	Other
With remote control	No
Remote operation possible	No
Average nominal lifespan [h]	15000
Weighted energy consumption in 1000 hours [kWh]	1
Min. number of switching cycles	15000
Energy efficiency class	G
Lamp designation	Other
Energy Efficiency Index (EEI)	80
Degree of protection (IP)	IP20
Length [mm]	57
Diameter [mm]	22
Dimmable	No
Colour consistency (McAdam ellipse)	SDCM6
Beam angle [°]	360 - 360
Colour housing	Colourless
Colour temperature [K]	2700 - 2700
Colour	White
Socket	BA15d
Colour of light according to EN 12464-1	Warm white <3300 K
Type of glass/cover	Clear
Filament lamp	Yes
Lamp shape	Tube, single-ended
Colour rendering index CRI	80-89
Lamp efficacy [lm/W]	55
Luminous flux [lm]	55 - 55
Voltage type	AC
Lamp power [W]	1 - 1
Power factor	0.3
Nominal current [mA]	10 - 10
Nominal voltage [V]	220 - 240

Alternative articles



142195

LED FIL T20X60
Ba15d DIM 2.5W
(18W) 170lm 827 Clear

80100037137

LED FIL P26X58
Ba15d 1W (14W)
120lm 827 Clear