



LED Spot PAR20 E27 7W 500lm 830 40D Alu DIM IP65

Article number 80100039963

BAI BaiSpot LED PAR20 E27 7W 3000K 40° Aluminum Reflector 500lm (75W)
Dimmable 230V-240V 63x79mm LED-lamp IP65 Cover only

The so-called LED spots from the BaiSpot series are characterized by a much longer lifespan and significantly less energy consumption than their halogen predecessors. Due to the compact design, they are easily interchangeable. Spots are mainly used to provide directed light from the ceiling or wall. This glass version literally and figuratively has an extra beautiful appearance because the part through which the light shines is made entirely of glass. Ambient temperature range: -20°C to +35°C.

General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	80100039963
Brand	Bailey
Productseries	BaiSpot LED MV
Product type	PAR20 Alu

ETIM specifications

IFTTT support available	No
Compatible with Amazon Alexa	No
Compatible with Google Assistant	No
Compatible with Apple HomeKit	No
Photobiological safety according to EN 62471	Other
With remote control	No
Remote operation possible	No
Average nominal lifespan [h]	25000
Weighted energy consumption in 1000 hours [kWh]	7
Min. number of switching cycles	15000
Energy efficiency class	A+
Lamp designation	PAR20
Energy Efficiency Index (EEI)	0.16
Degree of protection (IP)	IP65
Length [mm]	79
Diameter [mm]	63
Dimmable	Yes
Colour consistency (McAdam ellipse)	Other
Beam angle [°]	40 - 40
Colour housing	Grey
Colour temperature [K]	3000 - 3000
Colour	White
Socket	E27
Colour of light according to EN 12464-1	Warm white <3300 K
Type of glass/cover	Prism
Filament lamp	No
Lamp shape	Reflector
Colour rendering index CRI	80-89
Lamp efficacy [lm/W]	71
Luminous flux [lm]	500 - 500
Voltage type	AC
Lamp power [W]	7 - 7
Power factor	0.5
Nominal current [mA]	61 - 61
Nominal voltage [V]	220 - 240

Successor



145513

LED Spot PAR20 E27
DIM 7W (50W) 560lm
830 40D IP65