



LED PL 2G11 2S TC-L 15W (36W) 840 FR EM+AC

Article number 80100040747

BAI LED PL 2G11 TC-L 15W (36W) 4000K 1500lm Double-sided light Frosted 100V-240V 240° 44x422mm LED-lamp Alt PLL Dulux L

The LED PL 2G11 (4-pin) TC-L lamps with double-sided light are replacements for the commonly used compact fluorescent lamps without integrated ballast. PL stands for Public as these lamps are mainly used in public areas (indoor and outdoor) and as general lighting in shops, offices and hotels. Installation: Conventional ballast: Always remove the starter. Decoupling magnetic ballast is optional, not necessary. Electronic Ballast: Disconnect ballast before use. Ambient temperature range: -20°C to +40°C.

General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	80100040747
Brand	Bailey
Productseries	LED PL
Product type	2G11 4P

ETIM specifications

IFTTT support available	No
Compatible with Amazon Alexa	No
Compatible with Google Assistant	No
Compatible with Apple HomeKit	No
Photobiological safety according to EN 62471	Other
With remote control	No
Remote operation possible	No
Average nominal lifespan [h]	20000
Weighted energy consumption in 1000 hours [kWh]	15
Min. number of switching cycles	15000
Energy efficiency class	F
Lamp designation	Other
Energy Efficiency Index (EEI)	0.14
Degree of protection (IP)	IP20
Length [mm]	422
Diameter [mm]	44
Dimmable	No
Colour consistency (McAdam ellipse)	Other
Beam angle [°]	240 - 240
Colour housing	White
Colour temperature [K]	4000 - 4000
Colour	White
Socket	2G11
Colour of light according to EN 12464-1	Neutral white 3300-5300 K
Type of glass/cover	Frosted
Filament lamp	No
Lamp shape	Tube, single-ended
Colour rendering index CRI	80-89
Lamp efficacy [lm/W]	100
Luminous flux [lm]	1500 - 1500
Voltage type	AC
Lamp power [W]	15 - 15
Power factor	0.9
Nominal current [mA]	200 - 200
Nominal voltage [V]	100 - 240

Alternative articles



80100038475

LED PL TC-L 2G11 4P
15W (36W) 1500lm
840 FR EM+AC