

SPIRALED Plus A110 E40 DIM 15W 720lm 922 Clear

Article number 80100040802

BAI spiraled Plus A110 E40 15W 2200K Clear 720lm (55W) Dimmable 230V-240V CRI90-100 280° 110x235mm Decorative bulb LED Filament

Especially for places where the lamp can be beautiful but also needs to provide a lot of light (eg with high ceilings or in traditional chalice luminaires), Bailey has added Spiraled Plus lamps with an industrial shape to the already impressive Spiraled® collection. The lamps are energy efficient and last a long time. these lamps can be dimmed with the right LED dimmer. Spiraled® is a protected brand name.



General ETIM properties

ETIM group	Lamps
ETIM class	LED-lamp/Multi-LED
Name	80100040802
Brand	Bailey
Productseries	Spiraled
Product type	Plus

ETIM specifications

IFTTT support available	No
Compatible with Amazon Alexa	No
Compatible with Google Assistant	No
Compatible with Apple HomeKit	No
Photobiological safety according to EN 62471	Other
With remote control	No
Remote operation possible	No
Average nominal lifespan [h]	15000
Weighted energy consumption in 1000 hours [kWh]	15
Min. number of switching cycles	100000
Energy efficiency class	G
Lamp designation	Other
Energy Efficiency Index (EEI)	0.25
Degree of protection (IP)	IP20
Length [mm]	235
Diameter [mm]	110
Dimmable	Yes
Colour consistency (McAdam ellipse)	Other
Beam angle [°]	280 - 280
Colour housing	Colourless
Colour temperature [K]	2200 - 2200
Colour	White
Socket	E40
Colour of light according to EN 12464-1	Warm white <3300 K
Type of glass/cover	Clear
Filament lamp	Yes
Lamp shape	Pear-shape
Colour rendering index CRI	90-100
Lamp efficacy [lm/W]	48
Luminous flux [lm]	720 - 720
Voltage type	AC
Lamp power [W]	15 - 15
Power factor	0.8
Nominal current [mA]	74 - 74
Nominal voltage [V]	220 - 240