



Part Number: 9222

50Ω Triax RG-58A/U Type, #20, PO, TC Braids, PVC Jkt

Product Description

50 Ohm Triax RG-58A/U Type, 20 AWG stranded (7x28) .037" tinned copper conductor, polyethylene insulation, double tinned copper braid shields (95% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	7x28	TC - Tinned Copper	0.038 in	1

Conductor Count:	1
Conductor Size:	20 AWG

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.12 in

Inner Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	TC - Tinned Copper	95 %

Inner Jacket Material

Material	Nominal Diameter
PE - Polyethylene	0.177 in

Outer Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	TC - Tinned Copper	95 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.241 in	0.021 in
	0.216 in	

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	4.7 Ohm/1000ft	4.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
30.8 pF/ft

Shielding:	Braid(s)
------------	----------

Inductance

Nominal Inductance
0.077 μH/ft

Impedance

Nominal Characteristic Impedance

50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
10 MHz	1.5 dB/100ft
50 MHz	3.3 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	7.2 dB/100ft
400 MHz	12 dB/100ft
500 MHz	14 dB/100ft
700 MHz	18 dB/100ft
900 MHz	22 dB/100ft
1000 MHz	24 dB/100ft

Delay

Max. Delay Skew

66 ns/100m

Nominal Velocity of Propagation (VP) [%]

66 %

Voltage

Non-UL Voltage Rating

1400 V RMS

Temperature Range

Non-UL Temp Rating:	75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	39 lbs/1000ft
Max Recommended Pulling Tension:	83 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

CPR Euroclass:	Fca
RG Type:	58A/U Type
RG / Series Type:	58A/U Type

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
9222 004100	Yellow	
9222 004500	Yellow	C
9222 004U500	Yellow	

Footnote: C - CRATE REEL PUT-UP.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.