

NESIGN®
Illuminating led

B.
Berker Business Solutions



171436712509 D

DIMMER 9-48V DC, LED- 96W WITH PUSH-BUTTON SWITCH POLAR WHITE GLOSSY, INTEGRO FLOW, NO CONTACT

DC dimmer in kit with a Berker Integro push-button switch for use with incandescent, halogen or LED lights/strips.

Perfect for RVs, caravans, trailers, boats, cars, trucks, or anywhere 9- 48VDC is present.

Accurate and flicker free dimming to very low intensity. No minimum load.

Connect any number of DC dimmers to a single push-button switch.

Connect any no of push-button switch to dimmer.

Press dimmer switch once to turn on or off. The dimmer has memory function and returns to previous dimming when turned on.

Press and hold switch to dim up or down and release at desired level.

9-48VDC, 96W, IP20

Temperature range: -5 - + 45° C

Measures: 36 x 36 x 12 mm

Cable lengths: 60 mm

EMC CISPR 15 (2018-05 ED.9.00), IEC 61547 (2009)

Safety IEC 61347-2-13:2014/AMD1:2016 with IEC 61347-1:2015

CE/EU Conformance Directive 2014/35/EU, Directive 2014/30/EU

Product Properties:

Dimensions:

Unit	pcs
------	-----

MOQ	1 .
-----	-----

Approvals:**Compliance:****Other information:**

Trademark	NESIGN, Berker
-----------	----------------

ETIM-Class	EC000025 - Dimmer
------------	-------------------

ETIM-Release	8.0
--------------	-----

Product Group	Dimmers
---------------	---------

Search Description	DIMMER 9-48V DC, 96W MED TRYCKKNAPPSBRYTARE
--------------------	---

Alternative SKU	171436712509D
-----------------	---------------

Logistic information:

Barcode	733117637033
---------	--------------

Country of origin	DE
-------------------	----

Item status	Non Stock Item, can be on stock but is not a regular stock item.
-------------	--

Stock code	171436712509 D
------------	----------------

Taric code	85389099
------------	----------

Unit	pcs
------	-----

MOQ	1 .
-----	-----