					Cutting capac			city	
No.	Length	Head width	Finish		Wire	mm	Ø	Weight	
	mm	mm			soft	medium	hard	g	
End cutte	ers								
with slim, j	pointed h	nead, spec	ial fl at cutt	ing edą	ge				
and adjust	table sto	p screw							
3-981-15	135	10	ultra flush		0.8	0.6	-	80	
Oblique t	op cutte	ers							
Cutting su	rface an	gled by 35	°, for flush	cutting	g, for				
horizontal	and vert	ical use.							
3-985-15	130	10	flush	1.2	1.0	-	75		
Wire load		• for oido o	uttore (to re	trofit)					

## Wire lead catcher for side cutters (to retrofit)

3-999-1	3-961-15 to 3-969-15 ( 10 mm head width )	9
3-999-2	3-971-15 to 3-973-15 ( 12.5 mm head width)	9





3-981-15

3-985-15



3-999

## **GRIPPING PLIERS**

Round nose pliers extremely slim									
3-991-15	130	10	short plain jaws	75					
Flat nose plier extremely slim									
3-992-15	130	10	short plain jaws	75					
Snipe nos extremely	slim								
3-996-15	140	10	short plain jaws	80					






3-992-15

3-991-15



3-996-15



## 4 pliers from the TECHNICline series 2 ESD Tweezers

lined up on the ESD tool holder VARIO for mounting or hanging

Content:Side cutters Art. No. 3-963-15, End cutters Art. No. 3-981-15,<br/>Flat nose pliers Art. No. 3-992-15, Snipe nose pliers Art. No. 3-996-15,<br/>2 ESD Tweezers, straight Art. No. 5-055-13 and curved Art. No. 5-078-13

