

## ULTRA-FINE TWEEZERS

### WITH MICROSCOPICALLY

01

**FINE TIPS** 

### **HIGH-TECH TWEEZER:**

- for a high-precision gripping thanks to ultra-fine 0.2 mm (+/-0.05) tips
- for working with very small, sensitive components
- for positioning and holding tasks under microscopes
- for working in laboratories and medical facilities
- for watchmakers



#### Stainless steel tweezers with a finepolished, matt and non-reflecting surface, also antimagnetic and acid-resistant.

0.2 mm fine precision tip

| Article No.  | Description  |
|--|--|
| 5-070-UF   | Set of tweezers in a handy wallet, 6-pcs., content:  |
| 5-049-UF<br>5-051-UF<br>5-052-UF<br>5-055-UF<br>5-072-UF<br>5-078-UF | straight, very sharply pointed, 110 mm, 4 SA<br>straight pointed, 120 mm, 2 SA<br>bent, very sharply pointed 110 mm, 5b SA<br>sickle-shaped, very sharply pointed, 120 mm, 7a SA<br>narrow straight pointed, 110mm, 3c SA<br>tapering, chisel, 130mm, PSF SA |

All tweezers also individually available!



ALSO AVAILABLE WITH ESD COATING

SEE NEXT PAGE!



# ULTRA-FINE TWEEZERS WITH MICROSCOPICALLY

01

0.2 mm fine

### FINE TIPS

| BERNSIEI        | •           | (           | (           | A           |             |
|-----------------|-------------|-------------|-------------|-------------|-------------|
| <br>5-049-UF-13 | 5-051-UF-13 | 5-052-UF-13 | 5-055-UF-13 | 5-072-UF-13 | 5-078-UF-13 |

**ESD** 

ESD precision tweezers in a handy and dissipative wallet. For complex gripping, positioning and holding tasks in laboratories, test units, and under microscopes.

## Stainless steel tweezers with dissipative ESD coating, antimagnetic and acid-resistant!

| Article No.  | Description  |  |  |  |  |
|--|--|--|--|--|--|
| 5-070-UF-13  | Set of tweezers in a handy case, 6-pcs., content:  |  |  |  |  |
| 5-049-UF-13<br>5-051-UF-13<br>5-052-UF-13<br>5-055-UF-13<br>5-072-UF-13<br>5-078-UF-13 | straight, very sharply pointed, 110 mm, 4 SA<br>straight pointed, 120 mm, 2 SA<br>bent, very sharply pointed 110 mm, 5b SA<br>sickle-shaped, very sharply pointed, 120 mm, 7a SA<br>narrow straight pointed, 110mm, 3c SA<br>tapering, chisel, 130mm, PSF SA |  |  |  |  |

All tweezers also individually available!