

WRENCHES, SOCKET WRENCHES SPECIAL WRENCHES

6-600 Combination wrench set, 7 pcs.

Content: 7-pcs combination wrenches 6 - 7 - 8 - 9 - 10 - 11 and 13 mm
Weight: 290 g



6-600

6-750 Double open-ended wrench, extra slim, 6 pcs. in plastic wallet

Material: chrome vanadium, nickel-plated
Content: 4 pcs. 3.0 x 3.5 - 4.0 x 4.5 - 5.0 x 5.5 - 6.0 x 6.5 mm
material thickness 1.5 mm, 120 mm long
2 pcs. 7.0 x 8.0 and 9.0 x 10.0 mm
material thickness 2.0 mm, 120 mm long
Weight: 85 g



6-750

Adjustable wrench

chrome-vanadium, chrome-plated

No.	Jaw-opening mm	Total length mm	Jaw length mm	Weight g
6-771	0 - 13	100	12	55
6-772	0 - 19	150	22	135
6-773	0 - 24	200	25	265



6-772

NEW

4-909 Bit-Screwdriver B-PEN



Material: made of high-quality Gun-Metal with powder coating in metallic grey.
The set consists of 22 bits and a bit holder in handy pen design and one magnetic cap with clip. The magazine can be equipped with 5 bits individually.
The remaining bits can be stowed in the practical plastic holder.

Content:

- Square S 1
- Pentalobe P 2, P 5, P 6
- ★ Torx Security T 8, T 9, T 10
- ★ Torx 5, 6, 7
- ⊕ Cross-slot 00, 0, 1
- ⊖ Slot 1.5, 2.0, 2.5, 3.0
- Hexagon 0.9, 1.3, 1.5, 2.0
- Sim-Eject-Bit 0.8



4-909