BERNSTEIN

MEASURING TOOLS

Handle-Ø

No.	i lariale 6	NCCUIC D	rotai icrigiti	vvcigiti
	mm	mm	mm	g
Scriber				
with rough	nened nickeled hand	lle, needles hardened	l and burnished, interc	hangeable
7-521	6	2.5	200	26
No.		Length mm		Weight g
made from	e vel n plastic with 3 level:	s: horizontal, vertical a	and 450 angle	
- made from 7-535		s: horizontal, vertical a	and 450 angle	58
7-535	n plastic with 3 level:		and 450 angle	58
7-535			and 450 angle Blatt	58 Weight g
7-535 No.	n plastic with 3 level: Messbereich	200		
	n plastic with 3 level: Messbereich gauge	200		

Needle-Ø

Total length

Weight



7-515

GAS SOLDERING IRONS

The progressive gas soldering iron is suitable for laboratories, service and production.

8-376 Gas soldering iron "PIEZO INDY 75"

adjustable gas supply 15-75 W, max. temperature approx. 580 $^{\circ}\text{C}$



DESOLDERING PUMPS

Desoldering pump PRAKTIK

Handy desoldering pump in all-metal housing with replaceable teflon tip, high suction by double sealing of the piston, colour: gold

 $\textbf{8-390} \quad \textbf{Desoldering pump} \ 195 \, \text{mm long,} \ \emptyset \ 20 \, \text{mm}$



8-390

8-238 SMD Vacuum pick-up Vampir

For easy, safe and precise handling of SMD components dissipative execution complete with bent nozzle and suction cups 3, 4, 6 and 9mm

