



# THE SLEEK WAY to Back It and Run



## Clean Lines, Polished Practicality

With a polished finish on the surface, this is one smooth flash drive. The keyhole design allows for convenient attachment to keychains or bags, so it's always with you on the move.

## More Power With USB 3.2 Gen 1

This sleek USB-A on-the-go flash drive is equipped with a USB 3.2 Gen 1 interface, which allows for speedy data transfers. With up to 256GB of storage capacity, you'll have more than enough space to take what you need with you.

USB FLASH DRIVE

## Blaze B32

16GB | 32GB | 64GB | 128GB | 256GB

### Features

- Super-speed data transfer with USB 3.2 Gen 1 interface
- Up to 256GB of storage capacity
- Sleek polished finish for a smooth visual appeal
- Convenient keyhole design for easy attachment to keychains or bags
- True Plug & Play Technology eliminates the need for external power
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, music, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

### Specifications

- Capacity: 16GB, 32GB, 64GB, 128GB, 256GB
- Dimensions: 65.3mm x 18.3mm x 8.4mm
- Weight: 9g
- Color: White
- Material: Plastic
- Interface: USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- OS Compatibility: Windows 11/10/8.1/8/7/XP, Mac OS 10.3.x and above, Linux 2.6.x and above
- Operating Temperature: 0°C - 70°C
- Certification: BSMI, CE, FCC, KC, EAC
- Warranty: 5 year limited warranty