



3D-ridged Design on Aluminum Alloy Casing



Photographers, videographers, designers, and creators will be delighted with the military-grade shockproof portable SSD, the Bolt B75 Pro. Its aluminum alloy material provides great heat dissipation, while its 3D ridges provide a barrier from scratches and fingerprints. Plus, the embedded L-shaped wraparound LED indicator gives clear indication of the data transfer status from nearly any angle.

USB Gen 2 Extreme High-Speed



Wrapped in a sleek and slim aluminum body that's both shockproof and scratchproof, the Bolt B75 Pro is a wondrous design you cannot put down. And when you do, it shines from the inside too. The Bolt B75 Pro has huge storage capacity (256GB/512GB/1TB/2TB/4TB) and reads and writes at blistering speeds (up to 520 and 420MB/s respectively). This USB 3.2 Gen 2 portable SSD can also transfer data up to a lightning fast 10Gbp/s.

Portable Solid State Drive Bolt B75 Pro

Features

- Rapid data transfer with USB 3.2 Gen 2 extreme high-speed interface (max. up to 10Gbps)
- Military-grade shockproof (122cm) portable solid state drive
- 3D ridged design for protection against scratches and fingerprints
- Made of lightweight aluminum with superior heat dissipation
- Slim L-shaped LED status light that can be seen from the top and front
- Includes 2 USB 3.2 fast sync and charge cables (Type-C to Type-C and Type-C to Type-A)
- Free SP Widget software download available for backup and restore, AES 256-bit encryption, and cloud storage

Specifications

- Dimensions: 124.4 x 82.0 x 12.2mm
- Weight: 68~85g (by capacity)
- Material: Aluminum
- Color: Black
- Performance Read (max.) : Up to 520MB/s
- Performance Write (max.) : Up to 420MB/s
- Interface: USB 3.2 Gen 2 (USB 3.1 Gen 2, USB 3.1 Gen 1 & USB 3.0, USB 2.0 backwards-compatible)
- Cable: Type-C to Type-C and Type-C to Type-A
- Supported OS: Windows 11/10/8.1/8/7/Vista/XP, Mac OS 10.3.x or later, Linux 2.6.x or later, Android OS 6.0 or later
- Operating temperature: 0°C~70°C
- Certification: CE/FCC/BSMI/UKCA/WEEE/RoHS/KCC
- Warranty: 3 years Limited

256GB | 512GB | 1TB | 2TB | 4TB