

# Euromas Aluminium / Euromas F05

Enclosure, aluminium



A 125

Order no.: 01125000

\* = Available on request.

## Characteristics

Colour of enclosure group

Grey, similar to RAL 7001

Protection class

IP 66

Enclosure Material

G Al Si 12, PU foamed seal

For details see Technical Information

## Dimensions

Dimensions

160 x 160 x 91 mm

Product drawing

[01125000\\_A-125.pdf](#)

## Scope of delivery

Lid and base, lid screws (V2A), 4 screws for installation/earthing

## Note

On the A 198, because of the wall-mounting drill holes inside the sealed lip, expert sealing of the wall-mounting is necessary to achieve protection class IP 66.

G = design with transparent lid (PC)

## Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

17.02.2022

## Technical documentation / Downloads

---

### Technical drawings

3D product data in STEP format: Registration necessary  
Drawing for mechanical processing: 01125000 A-125-G.dxf (308.2 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product drawing in PDF format: 01125000 A-125.pdf (81.0 KB)  
Product drawing in DXF format: 01125000 A-125.dxf (536.6 KB)

### Works Test Certificates

682 WPZ-Euomas-Aluminium DE.pdf (163.7 KB)  
682 WPZ-Euomas-Aluminium EN.pdf (143.7 KB)

### Product information

Euomas Aluminium F05 GB.pdf (1.8 MB)