

2 608 644 133 – Circular saw blade Expert for High Pressure Laminate

Material number	2 608 644 133
EAN	3165140796996
Packaging type	Paper / Cardboard / Corrugated board - Packaging, tube, with Euro hole
Pack quantity	1 Pcs
Minimum order quantity	1 Pcs



Technical data

Description

Product line	PRO accessories
Specification	165 x 20 x 2,6 mm, 48



Details

Outer diameter mm	165
Bore size mm	20
Width of cut (b1) mm / Base bl. thickness (b2) mm	2.6/1.6
Number of teeth	48
Tooth shape	HLTCG
Max. rotation speed (RPM)	11500
Cutting result	4
Pin hole/Pitch circle diameter	2/6/32,5
Hook angle ° w1	0
Relief angle ° w2	17

Appropriate for

Materials that can be processed (Detail)	Pressed laminated wood
--	------------------------