

0 611 910 073 – GBH 18V-26 F

Material number	0 611 910 073
EAN	4059952647487



Technical data

Description

Trades	Construction Electrician Landscaping Plumbing, heating and air conditioning technology Joiners and carpenters
Cordless/Corded	Cordless
Tool dimensions (width)	378 mm
Tool dimensions (length)	225 mm
Tool dimensions (height)	225 mm
Packaging dimensions (width x length x height)	360 x 445 x 155 mm
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level 88 dB(A); Sound power level 99 dB(A). Uncertainty K= 3 dB.

Technical data

Impact energy (according to EPTA 05/2016)	2.6 J
Impact rate at rated speed	0 – 4,350 bpm
Rated speed	0 – 980 rpm
Battery voltage	18.0 V
Tool holder	SDS plus

Drilling range

Drilling dia. concrete, hammer drill bits, from	4 mm
Drilling dia. concrete, hammer drill bits, up to	26 mm
Hammer drilling diameter range in concrete	4 – 26 mm
Recommended drilling diameter range in concrete	8 – 16 mm
Max. drilling diameter in metal	13 mm
Max. drilling diameter in wood	30 mm

Noise/vibration information

Sound pressure level	88 dB(A)
Sound power level	99 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- Universal rotary hammer with quick-change chuck in the SDS plus cordless category

User benefit

- Optional GDE 18V-16 Professional dust extraction unit integrates with the hammer for a self-contained HEPA dust solution
- KickBack Control and Electronic Precision Control for better tool handling and increased user protection
- Delivers 2.6 J of impact energy for fast drilling and high chisel removal performance

