

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Impact Wrench

GDS 18V-1000 C



Powerful 1/2" cordless impact wrench with adjustable modes and BITURBO Brushless technology

The most important data

Battery voltage	18.0 V
Torque, max.	1,000 Nm
Screw diameter	M 14 - M 24

Part Number 0 601 9J8 000[> More product information](#)

Technical data

Technical data

Torque adjustment range, min./max., 1st level	0/350 Nm
Torque adjustment range, min./max., 2nd level	0/650 Nm
Torque adjustment range, min./max., 3rd level	0/1000 Nm
No-load speed	0-1,750 rpm
No-load speed (1st level)	0-800 rpm
No-load speed (2nd level)	0-1,300 rpm
No-load speed (3rd level)	0-1,750 rpm
Torque settings	3
Weight excl. battery	2.9 kg
Torque, max.	1,000 Nm
Impact rate	0-2,600 bpm
Impact rate (1st level)	0-1,600 bpm
Impact rate (2nd level)	0-2,300 bpm
Impact rate (3rd level)	0-2,600 bpm
Battery voltage	18.0 V
Tool holder	1/2" Square
Breakaway torque, max.	1,600 Nm
Packaging dimensions (width x length x height)	270 x 288 x 109 mm

Screw diameter

Screw diameter	M 14 - M 24
----------------	-------------

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	13.5 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- BITURBO Brushless technology providing 1,000 Nm tightening torque and 1,600 breakaway torque
- User interface with two default modes, metal (A) and wood (B). Additional modes can be adjusted and individualised via the Toolbox App
- More flexibility and control via three speed/torque settings

**BITURBO**
BRUSHLESS

powered by BOSCH