

**BOSCH**

Invented for life

# Product data sheet

## Power tools for trade & industry

Rotary Hammer with SDS plus

### GBH 2-21



So small, so strong – the compact and powerful entry-level rotary hammer

#### The most important data

Rated input power	720 W
Impact energy (according to EPTA 05/2016)	2 J
Drilling dia. concrete, hammer drill bits	4 – 22 mm

**Part Number** 0 611 2A6 061[> More product information](#)

## Technical data

### Performance data

Impact rate at rated speed	0 – 4,800 bpm
----------------------------	---------------

### Technical data

Rated input power	720 W
Impact energy (according to EPTA 05/2016)	2 J
Tool holder	SDS plus
Packaging dimensions (width x length x height)	360 x 397 x 115 mm
Weight	2.3 kg

### Drilling range

Drilling dia. concrete, hammer drill bits	4 – 22 mm
Max. drilling diameter in metal	13 mm
Max. drilling diameter in wood	30 mm

## Noise/vibration information

### Hammer drilling in concrete

Vibration emission value ah	14.7 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Powerful 720 W motor and 2.0 J of impact energy for effective hammer drilling in concrete (up to 21-mm diameter)
- Compact rotary hammer offers professional Bosch hammer drilling performance within reach
- Three-mode rotary hammer for hammer drilling, drilling, and chiselling ensures versatility and convincing results

