

# Specification - Brio 300

<b>Dimensions</b>	<p>WEBCAM DIMENSIONS</p> <p>Height x Width x Depth:</p> <p>2.58 in (65.63 mm) x 2.09 in (53.1 mm) x 1.78 in (45 mm), incl. mount clip</p> <p>Weight:</p> <p>2.63 oz (74.6 g), incl. mount clip &amp; cable</p> <p>Attached cable length:</p> <p>5 ft (1.5 m)</p>
<b>System Requirements</b>	<p><b>Required:</b> Available USB-C port</p> <p><b>Works with:</b> Windows, macOS, or Chrome OS* and virtually any popular videocalling platform.</p> <p>*Logi Tune not available for Chrome OS.</p> <p><b>Certified for:</b> Microsoft Teams, Zoom, Google Meet, Works With Chromebook.</p> <p><b>Compatible with:</b></p> <ul style="list-style-type: none"><li>• Windows 10 and later</li><li>• macOS 10.15 and later</li><li>• Chrome OS</li></ul> <p>(2GB RAM or more needed for 1080p video streaming and 1GB RAM is typically needed for streaming 720p)</p>

<b>Technical Specifications</b>	<p>Multiple resolutions:</p> <ul style="list-style-type: none"> <li>• 1080p/30fps (1920x1080 pixels)</li> <li>• 720p/30fps (1280x720 pixels)</li> <li>• Camera megapixel: 2MP with High Dynamic Contrast</li> <li>• Focus type: Fixed focus</li> <li>• Lens type: Custom Logi 4 element lens with anti-reflective coating</li> <li>• Diagonal field of view (dFoV): 70°</li> </ul> <p>Built-in Microphone type:</p> <ul style="list-style-type: none"> <li>• Type: Single, digital noise reducing microphone</li> <li>• Mic range: Up to 4m</li> </ul> <p>Integrated privacy shutter</p> <p>USB connectivity: USB-C plug-and-play</p> <p>Supported in Logi Tune</p> <p>RightLight 2 Auto light correction</p>
<b>Warranty Information</b>	<ul style="list-style-type: none"> <li>• AMR - 1 year</li> <li>• AP - 1 year</li> <li>• EMEA - 2 years</li> <li>• JP - 1 year</li> </ul>
<b>Package Contents</b>	<ul style="list-style-type: none"> <li>• Camera with attached USB-C cable</li> <li>• Warranty and legal information</li> </ul>