

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Hexagonal Keys
Catalogue number	4404, 4405, 4407, 4411, 4414, 4415, 4416, 4417, 4443M, 4444L & 4874X
Date	19/02/2009

Range Description

A range of professional quality Hexagonal Keys

Features

All

- Made from Chrome Vanadium steel
- Hardened and tempered for strength and durability



4404A/4405A



4407



4411



4414



4415/4416



4443M



4444L

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4404A	Hexagon Key Metric Set/7	5013969019308	82041100	6
T4405A	Hexagon Key A/F Set/7	5013969019315	82041100	6
T4407	Hexagon Key Torx Set/8	5013969985375	82041100	12
T4411 007	Hexagon Key 0.7mm	5013969700893	82041100	12
T4411 009	Hexagon Key 0.9mm	5013969700909	82041100	12
T4411 01	Hexagon Key 1mm	5013969700916	82041100	12
T4411 012	Hexagon Key 1.2mm	5013969700923	82041100	12
T4411 0127	Hexagon Key 1.27mm	5013969700930	82041100	12
T4411 015	Hexagon Key 1.5mm	5013969700947	82041100	12
T4411 02	Hexagon Key 2mm	5013969700954	82041100	12
T4411 025	Hexagon Key 2.5mm	5013969700961	82041100	12
T4411 03	Hexagon Key 3mm	5013969700978	82041100	12
T4411 035	Hexagon Key 3.5mm	5013969700985	82041100	12
T4411 04	Hexagon Key 4mm	5013969700992	82041100	12

T4411 045	Hexagon Key 4.5mm	5013969701005	82041100	12
T4411 05	Hexagon Key 5mm	5013969701012	82041100	12
T4411 055	Hexagon Key 5.5mm	5013969701029	82041100	12
T4411 06	Hexagon Key 6mm	5013969701036	82041100	12
T4411 07	Hexagon Key 7mm	5013969701043	82041100	12
T4411 08	Hexagon Key 8mm	5013969701050	82041100	12
T4411 09	Hexagon Key 9mm	5013969701067	82041100	12
T4411 10	Hexagon Key 10mm	5013969701074	82041100	12
T4411 11	Hexagon Key 11mm	5013969701081	82041100	12
T4411 12	Hexagon Key 12mm	5013969701098	82041100	6
T4411 13	Hexagon Key 13mm	5013969701104	82041100	6
T4411 14	Hexagon Key 14mm	5013969701111	82041100	3
T4411 15	Hexagon Key 15mm	5013969701128	82041100	3
T4411 16	Hexagon Key 16mm	5013969701135	82041100	3
T4411 17	Hexagon Key 17mm	5013969701142	82041100	3
T4411 18	Hexagon Key 18mm	5013969701159	82041100	3
T4411 19	Hexagon Key 19mm	5013969701173	82041100	3
T4411 20	Hexagon Key 20mm	5013969701173	82041100	3
T4411 22	Hexagon Key 22mm	5013969701180	82041100	3
T4414	Hexagon Key A/F Set/8	5013969570601	82041100	6
T4415	Hexagon Key A/F Set/10	5013969570700	82041100	6
T4416	Hexagon Key 1.5-10mm Set/10	5013969570809	82041100	6
T4417	Hexagon Key 1.5-7mm Set/8	5013969570908	82041100	6
T4443M	Hexagon Key Metric Set/10	5013969121407	82041100	6
T4444I	Hexagon Key A/F Set/9	5013969121803	82041100	6

Technical product information	
Standards compliance	Manufactured to DIN9111
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Loose keys – Germany Sets – Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4404A	35	32	111	292	75	40	195	312
T4405A	35	32	111	334	75	40	195	352
T4407	18	27	97	140	67	30	225	160
T4411 007	5	1	30	0.1	-	-	-	-
T4411 009	5	1	30	0.1	-	-	-	-
T4411 01	5	1	30	0.1	-	-	-	-
T4411 012	15	1	45	0.2	-	-	-	-
T4411 0127	15	1	45	0.2	-	-	-	-
T4411 015	15	2	45	0.3	-	-	-	-
T4411 02	17	2	50	0.5	-	-	-	-
T4411 025	20	3	60	1	-	-	-	-
T4411 03	20	3	65	4	-	-	-	-
T4411 035	20	4	65	6	-	-	-	-
T4411 04	30	4	75	10	-	-	-	-
T4411 045	30	5	75	12	-	-	-	-
T4411 05	30	5	85	16	-	-	-	-
T4411 055	35	6	90	22	-	-	-	-
T4411 06	35	6	95	28	-	-	-	-
T4411 07	40	7	100	40	-	-	-	-
T4411 08	45	8	105	56	-	-	-	-
T4411 09	50	9	110	76	-	-	-	-
T4411 10	50	10	120	102	-	-	-	-
T4411 11	50	11	125	128	-	-	-	-
T4411 12	55	12	135	162	-	-	-	-
T4411 13	60	13	135	204	-	-	-	-
T4411 14	65	14	150	252	-	-	-	-
T4411 15	70	15	160	308	-	-	-	-
T4411 16	75	16	160	360	-	-	-	-
T4411 17	75	17	170	426	-	-	-	-
T4411 18	80	18	180	510	-	-	-	-
T4411 19	85	19	190	605	-	-	-	-
T4411 20	90	20	200	700	-	-	-	-

T4411 22	100	22	220	923	-	-	-	-
T4414	50	10	110	94	75	20	180	110
T4415	80	10	160	244	85	25	215	266
T4416	55	25	140	292	85	25	215	310
T4417	55	25	120	120	80	25	180	138
T4443M	85	14	180	388	100	15	265	420
T4444I	85	14	180	338	100	15	265	370

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4404A	150	245	100	2005		
T4405A	150	245	100	2240		
T4407	230	310	90	2070		
T4411 007	40	2	80	2		
T4411 009	40	2	80	2		
T4411 01	60	2	100	4		
T4411 012	40	2	80	6		
T4411 0127	40	2	80	6		
T4411 015	60	2	100	10		
T4411 02	60	2	100	20		
T4411 025	60	3	100	38		
T4411 03	60	3	100	58		
T4411 035	80	4	130	82		
T4411 04	80	4	130	120		
T4411 045	80	5	130	146		
T4411 05	80	5	130	195		
T4411 055	100	6	170	245		
T4411 06	100	6	170	341		
T4411 07	100	15	170	485		
T4411 08	100	15	170	677		
T4411 09	100	15	170	917		
T4411 10	80	200	50	1260		
T4411 11	80	200	50	1572		
T4411 12	80	200	50	1008		

T4411 13	80	200	50	1260		
T4411 14	80	200	50	792		
T4411 15	80	200	50	960		
T4411 16	80	200	50	1116		
T4411 17	85	230	50	1334		
T4411 18	85	230	50	1586		
T4411 19	85	230	50	1871		
T4411 20	95	260	50	2156		
T4411 22	105	360	70	2881		
T4414	125	190	95	750		
T4415	150	240	100	1743		
T4416	150	240	100	1950		
T4417	150	200	80	928		
T4443M	100	290	110	2630		
T4444I	100	290	110	2330		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4404A	8	Blister	10	Card			128	Box
T4405A	8	Blister	10	Card			128	Box
T4407	8	Blister	2	Card			150	Box
T4411 007					1	Bag		
T4411 009					1	Bag		
T4411 01					1	Bag		
T4411 012					1	Bag		
T4411 0127					1	Bag		
T4411 015					2	Bag		
T4411 02					2	Bag		
T4411 025					2	Bag		
T4411 03					2	Bag		
T4411 035					3	Bag		
T4411 04					3	Bag		
T4411 045					3	Bag		
T4411 05					3	Bag		

T4411 055					3	Bag		
T4411 06					5	Bag		
T4411 07					5	Bag		
T4411 08					5	Bag		
T4411 09					5	Bag		
T4411 10							36	Box
T4411 11							36	Box
T4411 12							36	Box
T4411 13							36	Box
T4411 14							36	Box
T4411 15							36	Box
T4411 16							36	Box
T4411 17							56	Box
T4411 18							56	Box
T4411 19							56	Box
T4411 20							72	Box
T4411 22							112	Box
T4414	8	Blister	10	Card			90	Box
T4415	8	Blister	10	Card			90	Box
T4416	8	Blister	10	Card			100	Box
T4417	8	Blister	10	Card			110	Box
T4443M	14	Blister	18	Card			110	Box
T4444I	14	Blister	18	Card			110	Box